



### Main

Range of product	Harmony XAR
Product or component type	Hand-held remote control
Device short name	ZART
Control button type	6 configurable motion push-button 6 configurable auxiliary push-button

### Complementary

Material	Enclosure : PC (polycarbonate) Enclosure : PBT (polybutylene terephthalate) Cover : PP (polypropylene) Protective cover : EPDM rubber
Function available	Accelerometer function Vibrator function
Display type	LCD display 34 x 42 mm
Operating distance	50 m
Mechanical robustness	4.5 m free fall resistance conforming to IEC 60068-2-27
Communication network type	Wireless : Bluetooth low energy
Transmission frequency	2.4 GHz
Maximum sensing distance	100 m in free field
Response time	< 300 ms at full duplex
Charging time	900 s
Autonomy	30 h
Battery type	Rechargeable
Mechanical durability	5000000 cycles
Service life	5 yr
Width	100 mm
Height	340 mm
Depth	90 mm
Product weight	0.65 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Environment

Radio agreement	RSS ARIB FCC SRRC ANATEL ICASA
IP degree of protection	IP65
NEMA degree of protection	NEMA 4
Ambient air temperature for operation	> -20...60 °C
Ambient air temperature for storage	> -20...45 °C
Operating altitude	0...2000 m
Storage altitude	0...3000 m
Vibration resistance	0.075 mm (f= 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Relative humidity	0...95 % (temperature : > -20...60 °C) (operating)
Product certifications	CE JIS UL KC C-Tick EAC CSA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1415 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Available