



## Purchase

APC  
 NET8

## Overview

Model Name	APC Network SurgeArrest, 8 outlet
Includes	Cord management straps , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Barbados , Bermuda , Bahamas , Belize , Canada , Colombia , Costa Rica , Dominican Republic , Ecuador , Guatemala , Honduras , Haiti , Jamaica , Cayman Islands , Mexico , Nicaragua , Panama , Puerto Rico , El Salvador , Turks And Caicos Islands , Trinidad And Tobago , United States , Venezuela

## Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	1.83 meters

## Surge Protection and Filtering

Surge energy rating	1120 joules
Data Line Protection	--

## Physical

Maximum Height	44 mm
Maximum Width	203 mm
Maximum Depth	146 mm
Net Weight	0.86 kg
Shipping Weight	1 kg
Shipping Height	51 mm

Shipping Width	318 mm
Shipping Depth	159 mm
Master Carton Units	12.0
Master Carton Weight	29.5 lbs
Color	Beige
SCC Codes	10731304000843
Units per Pallet	240.0

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

### Conformance

Approvals	CSA , UL 1283 , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$100000