


Part Number : **1501535W3A**

Type	Size	Rating	Description
LED	T3	24V AC/DC	3mm Bi-pin LED Lamp

Dimensions(mm):



Colour	Current (mA)	Intensity (mcd)
Cool white	4/8	1400 ^[7]

Notes:

1	Colour Coordinates	X=0.31, y=0.32
2	Lens	Clear
3	Rectification	Half-wave
4	Voltage Tolerance	10%
5	Operating Temperature	-20 to +60 °C
6	Storage Temperature	-20 to +80 °C
7	Light Output	Luminous Intensity on DC