



3W

VT-2073 3W PLASTIC CANDLE BULB COLORCODE:2700K B22

Lumens 250	Beam Angle 200	Dimensions 37 x 102mm
----------------------	--------------------------	---------------------------------

Warm White
SKU:7230

2 YEARS
WARRANTY



Technical Information

Instant Start: 0-100% in 1t1s	LED Chip Type: SMD
Watts: 3	IP Rating: IP20
Lumens: 250	Dimmable: No
Holder Type: B22	Warranty (Years): 2
Shape: CANDLE	PF: >0.4
Beam Angle: 200	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: PLASTIC	Input Power: AC:220-240V,50Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

Features

- ✓ Stable SMD technology which makes the product more reliable and durable
- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ High endurance and Durability
- ✓ Excellent Heat Radiation Efficiency
- ✓ Aluminium & Thermoplastic Body options available
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Broad Range of holders like E27, E14, B22, B15
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge, etc.

Packaging

Unit Details

Length(Box)mm	40
Width(Box)mm	40
Height(Box)mm	105
Unit CBM	0.000208

Listing Details

EAN Code	3800157619578
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	200
Qty Per Pallet	625

www.vtacexports.com

2 YEAR **||||**
WARRANTY

CE/EMC

