

## PCRS\_LCAX\_LCAX\_A221T\_XX.X\_SS

### Description

Duplex patch cord, LC uniboot push-pull XD to LC uniboot push-pull XD, APC, duplex round 2.1mm\_XX.X\_yellow, SM G.657.A2, A-B / B-A



Features	Features
- High mechanical stability	
- Colour coded boot for good visibility also in mated condition	

### Technical Data

#### General Data

Description	Values
General Typ	Duplex LC patch cord
Operation temperature (in Work)	-45 up to 85
Polarity	A-B / B-A straight polarity (standard)
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes

#### Connector left

Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	APC
Color Housing	Black
Color Clip	Green
Color Boot	Black / Black
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	S
Return Loss	>85 dB
Durability	1000
Tensile load	70 N
Tensile load acc. To GR-326-COR	Fullfilled

#### Connector right


Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	APC
Color Housing	Black
Color Clip	Green
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	1S
Return Loss	>85
Durability	1000
Tensile load	70 N
Tensile load acc. To GR-326-COR	Fullfilled

#### Cable

Description	Values
Cable typ	Riser Cable

## PCRS\_LCAX\_LCAX\_A221T\_XX.X\_SS

Fiber count	2
Fiber	2 x 0.6mm
Fiber typ	E9/125-SM G.657.A2
Outer diameter	2.1 mm
Outer jacket material	Jacket material according to UL 94V-0
Outer jacket color	Yellow



### Ordering information

Attenuation (m)	Item number	Description
1.0	85020987	PCRS_LCAX_LCAX_A221T_01.0_S
2.0	85020988	PCRS_LCAX_LCAX_A221T_02.0_S
3.0	85020989	PCRS_LCAX_LCAX_A221T_03.0_SS
3.5	85020990	PCRS_LCAX_LCAX_A221T_03.5_S
5.0	85020991	PCRS_LCAX_LCAX_A221T_05.0_SS
6.0	85020992	PCRS_LCAX_LCAX_A221T_06.0_S
7.0	85020993	PCRS_LCAX_LCAX_A221T_07.0_S
10.0	85020994	PCRS_LCAX_LCAX_A221T_10.0_SS
15.0	85020995	PCRS_LCAX_LCAX_A221T_15.0_S
20.0	85020996	PCRS_LCAX_LCAX_A221T_20.0_S