

Model: XHC1080BAQ



Xvision XHD Professional 1080P AHD/CVI/TVI Hybrid IR Bullet Camera, 60m IR, UTC

Brand:	Xvision
Model Number:	XHC1080BAQ
Style:	Bullet Camera
Weather Resistant:	Yes
Vandal Resistant:	No
Mounting Type:	Wall or Ceiling
Dimensions (WHD in mm):	121x90x253
Weight (kg):	0.90
Warranty:	1 Year Warranty
Sensor Type:	1/2.8" Sony 2.43 Megapixel CMOS
DSP Type:	Xvision X3K DSP
DSP Functions:	Sens-up, DWDR, NR, Defog, DPC, Mirror, MD, Privacy Zone, AGC, White Balance
Resolution:	1080P/HD960H/HD-TVI/HD-CVI
Minimum Illumination:	0.0003 Lux
Night Vision:	60m IR
Lens Type:	Varifocal
Lens Size:	2.8-12.0mm
Viewing Angle:	23-92°
Operating Voltage:	12V DC - 560mA
Suggested Power Supply:	12V DC 1250mA
Video Output:	BNC Socket
Audio Output:	No
Power Input:	DC Socket
RS485 Control:	No