

Head Office:
 Xvision Group (UK)
 Beddington Farm Road
 Croydon, Surrey
 CR0 4WP
 United Kingdom

Korea:
 Kyoung Am Building
 157-27 Samsung-dong
 Kangnam-ku
 135 090 Seoul
 Korea

Model: XHC1080VVQ-G/W



Xvision XHD Professional 1080P AHD/CVI/TVI Hybrid Vandal IR Dome Camera, 40m IR, UTC,

Brand:	Xvision
Model Number:	XHC1080VVQ-G/W
Style:	Dome Camera
Weather Resistant:	Yes
Vandal Resistant:	Yes
Mounting Type:	Wall or Ceiling
Dimensions (WHD in mm):	120X95X120
Weight (kg):	1.0
Warranty:	1 Year Warranty (extendable to 3 years and advanced replacement period to 1 year)
Sensor Type:	1/2.8" Sony 2.43 Megapixel CMOS
DSP Type:	Xvision X3K DSP
DSP Functions:	Sens-up, DWDR, NR, Defog, DPC, Mirror, MD, Privacy Zone, AGC, White Balance
Resolution:	1080P/HD960H/HD-CVI/HD-TVI
Minimum Illumination:	0.0003 Lux
Night Vision:	40m IR
Lens Type:	Fixed
Lens Size:	2.8-12.0mm
Viewing Angle:	23-92°
Operating Voltage:	12V DC - 360mA
Suggested Power Supply:	12V DC - 1250mA
Video Output:	BNC Socket
Audio Output:	No
Power Input:	DC Socket
RS485 Control:	No