

Model: XC1080VVP-2-G/W



Xvision Professional – Full HD (1080P) Dome IP Camera, 40m IR

Brand	Xvision Professional HD IP
Model Number	XC1080VVQ-G/W
Style	Dome
Weather Resistant	Yes
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Dimensions (WHD in mm)	165x145x165
Weight (Kg)	1.0
Warranty	1 Year Limited Warranty
Sensor Type	Sony 2.43MP Sensor
DSP Type	Xvision X3K-IP DSP
DSP Functions	Automatic White Balance Automatic Gain Control Automatic Electronic Iris DNR (Digital Noise Reduction) WDR (Wide Dynamic Range)
Resolution	1920x1080
Minimum Illumination	0 Lux (IR on) 0.1 Lux (IR off)
Night Vision	40m IR Night Vision
Lens Type	Auto Iris IR Optimised
Lens Size	2.8-12mm
Viewing Angle	23-92°
Operating Voltage	12V DC
Suggested Power Supply	12V DC 1250ma
Video Output	RJ45
Audio Output	N/A
Power Input	DC Socket, PoE