

General Information

Extended Product Type:	FEMR8
Product ID:	1SNA116987R0200
EAN:	3472591169874
Catalog Description:	FEMR8 End Sections Grey
Long Description:	FEMR8 - End Sections - Grey - 2.8mm Spacing.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Country of Origin:	France (FR)
Customs Tariff Number:	39269097
EAN:	3472591169874
ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block
Environmental Information:	1SND220090E1000
Function:	End Sections
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Insulation Material:	Polyamide
Invoice Description:	FEMR8 End Sections Grey
Minimum Order Quantity:	10 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Object Classification Code:	X
Order Multiple:	10 piece
Package Level 1 EAN:	3472591169874
Package Level 1 Gross Weight:	0.03 kg
Package Level 1 Units:	10 piece
Package Level 2 Units:	1000 piece
Package Level 3 Units:	6000 piece
Product Main Type:	FEMR
Product Name:	End Section
Product Net Weight:	3 g
RoHS Information:	1SND230478F0202
Selling Unit of Measure:	piece
Spacing:	2.8 mm
Suitable For:	M4/6.RS M6/8.RS

