

## General Information

<b>Extended Product Type:</b>	BADRL
<b>Product ID:</b>	1SNA199420R2100
<b>EAN:</b>	3472591994209
<b>Catalog Description:</b>	BADRL End Stops - Grey
<b>Long Description:</b>	- Screwless, snaps on rail without tool, - Give efficient support to the SNA terminal blocks assemblies.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Grey
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>E-nummer:</b>	2940345
<b>EAN:</b>	3472591994209
<b>ETIM 4:</b>	EC001041 - End bracket for terminal block
<b>ETIM 5:</b>	EC001041 - End bracket for terminal block
<b>ETIM 6:</b>	EC001041 - End bracket for terminal block
<b>Flammability According to UL94:</b>	V0
<b>Function:</b>	End Stops
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Insulation Material:</b>	Polyamide
<b>Invoice Description:</b>	BADRL End Stops - Grey
<b>Minimum Order Quantity:</b>	50 piece
<b>Mounting on DIN Rail:</b>	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	50 piece
<b>Package Level 1 EAN:</b>	3472591994209
<b>Package Level 1 Gross Weight:</b>	0.1 kg
<b>Package Level 1 Length:</b>	280 mm
<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	185 mm
<b>Package Level 2 Units:</b>	1500 piece
<b>Package Level 3 Units:</b>	72000 piece
<b>Product Main Type:</b>	BADRL
<b>Product Name:</b>	End Stop
<b>Product Net Depth:</b>	17.5 mm
<b>Product Net Height:</b>	23.8 mm
<b>Product Net Weight:</b>	2 g
<b>Product Net Width:</b>	6.5 mm
<b>Product Packing Type:</b>	Bag
<b>Recommended Screw Driver:</b>	4 mm

<b>RoHS Date:</b>	20160314
<b>RoHS Information:</b>	1SND230479F0206
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	End Stops BADRL
<b>Spacing:</b>	6.5 mm
<b>Suitable For:</b>	DR1.5/4 DR1.5/5 DR1.5/6.ADO DR1/5.ADO DR2.5/10.4L DR2.5/10.P.4L DR2.5/5.2L DR2.5/5.ADO DR2.5/5.S DR2.5/8.ADO DR2.5/8.P.ADO DR4/6 DR4/6.1 DR4/6.ADO DR4/6.P DR4/8.A.ADO3 DR4/8.A.P.ADO3 DR4/8.ADO DR4/8.P.ADO DR4/8SF DRE1.5/6.ADO DRE1/5.ADO DRE2.5/5.ADO DRE2.5/8.ADO DRE4/6.ADO DRE4/8.A.ADO3 DRE4/8.ADO

