

## Basic

Brand Name:	HP
DisplayPort:	Yes
Form Factor:	Micro Tower
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	4
Number of USB 3.1 Ports:	4
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i3-7100
Processor Speed:	3.90 GHz
Processor Type:	Core i3
Product Family:	Business Desktop ProDesk 400 G
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Number of USB Ports:	8
VGA:	Yes

## Display & Graphics

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

## General Information

Brand Name:	HP
Manufacturer Part Number:	1EY27ET#ABU
Manufacturer Website Address:	<a href="http://www.hp.com">http://www.hp.com</a>
Manufacturer:	HP Inc.
Product Line:	Business Desktop
Product Name:	ProDesk 400 G4 Microtower PC
Product Series:	ProDesk 400 G4
Product Type:	Desktop Computer

## Interfaces/Ports

DisplayPort:	Yes
Number of DisplayPort Outputs:	1
Number of USB 2.0 Ports:	4
Number of USB 3.1 Ports:	4
Total Number of USB Ports:	8
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Features:	Security Slot
-----------	---------------

## Physical Characteristics

Depth:	274.1 mm
Form Factor:	Micro Tower
Height:	337.8 mm
Weight (Approximate):	5.47 kg
Width:	169.9 mm

## Power Description

Input Voltage:	120 V AC
----------------	----------

## Processor & Chipset

Processor Generation:	7th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-7100
Processor Speed:	3.90 GHz
Processor Type:	Core i3

## Software

Operating System Platform: Windows  
Operating System: Windows 10 Pro

**Storage**

Optical Drive Type: DVD-Writer  
Optical Media Supported: DVD±R/±RW