

Basic

Brand Name: HP
DisplayPort: Yes
Form Factor: Micro Tower
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 630
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Number of DisplayPort Outputs: 1
Number of USB 2.0 Ports: 4
Number of USB 3.1 Ports: 4
Operating System Platform: Windows
Operating System: Windows 10 Pro
Processor Manufacturer: Intel
Processor Model: i5-7500
Processor Speed: 3.40 GHz
Processor Type: Core i5
Product Family: Business Desktop ProDesk 400 G
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Number of USB Ports: 8
VGA: Yes

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 630
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM

General Information

Brand Name: HP
Manufacturer Part Number: 1EY28ET#ABU
Manufacturer Website Address: <http://www.hp.com>
Manufacturer: HP Inc.
Product Line: Business Desktop
Product Name: ProDesk 400 G4 Microtower PC (ENERGY STAR)
Product Series: ProDesk 400 G4
Product Type: Desktop Computer

Interfaces/Ports

DisplayPort: Yes
Number of DisplayPort Outputs: 1
Number of USB 2.0 Ports: 4
Number of USB 3.1 Ports: 4
Total Number of USB Ports: 8
VGA: Yes

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Features: Security Slot

Physical Characteristics

Depth: 274.1 mm
Form Factor: Micro Tower
Height: 337.8 mm
Weight (Approximate): 5.47 kg
Width: 169.9 mm

Power Description

Input Voltage: 120 V AC

Processor & Chipset

Processor Generation: 7th Gen
Processor Manufacturer: Intel
Processor Model: i5-7500
Processor Speed: 3.40 GHz
Processor Type: Core i5

Software

Operating System Platform: Windows

Operating System: Windows 10 Pro