

Screen Size

28"

Resolution

4K UHD (3840 x 2160)

Aspect Ratio

16:9

Response Time

1 ms

Refresh Rate

60 Hz

Colour Support

1.07 billion

Contrast Ratio

100,000,000:1

Brightness

300 cd/m²

Backlight

LED

Viewing Angles

170° horizontal

160° vertical

Panel Type

Twisted Nematic Film (TN Film)

Stand

Tiltable (-5° to 15°)

Ports & Connectors

DVI-in

HDMI@-in

Headphone

DisplayPort™

Power

41.50 W (ENERGY STAR® rating)

44 W (EEL)

450 mW (standby)

350 mW (off)

Environmental Certification

MPR II

Colours

Black

Tearing Prevention Technology

AMD FreeSync™

VESA Compatible

(Yes)

Dimensions (H x W x D)

5.91" x 10.20" x 1.02" (without stand)

7.5 inches x 10.2 inches x 3.3 inches (with stand)

Weight (Approximate)

11.2 lbs. (without stand)

12.4 lbs. (with stand)

Package Contents

RT280K Widescreen LCD Monitor

1 x DVI Cable

1 x Displayport Cable

Power Cord

Warranty