

## FAST AND FABULOUS

5.5" smartphone in a slim metal body, featuring 4G, advanced 13.0MP camera and powerful battery



- Beautiful design: slim metal body together with 2.5D curved screen glass ensure gorgeous look. Smartphone is available in trendy color options: golden and black
- Speed in your palm: 4G LTE Internet connection gives you ability to do more: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before
- High luminance wide display: high-precision 5.5" HD IPS screen displays colors with great clarity
- Photography: advanced 13.0MP camera with LED-flash ensures excellent clear & vivid images.
- High performance multitasking and energy saving: based on 64-bit quad core processor
- Huge battery: 3000 mAh powerful removable battery for maximum endurance
- Latest Android OS version: 7.0 Nougat
- Dual SIM: for optimizing budget on calls and Internet

<b>SIM card slot</b>	Dual SIM: LTE + WCDMA, 3FF micro SIM
<b>Display</b>	Size: 5.5" Resolution: HD (720 x 1280) Technology: IPS, 2.5D curved glass
<b>Processor</b>	MT6737 1.25 GHz 64-bit quad core
<b>Memory</b>	Built-in: 1 GB RAM + 16 GB eMMC Expandable: slot for microSD™ card up to 32GB
<b>Power</b>	3000 mAh Li-po Battery
<b>OS</b>	Android 7.0 Nougat
<b>Imaging</b>	Front: 2.0MP Rear: 13.0MP AF with LED flash

<b>Network</b>	4G LTE: 800/1800/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900 MHz
<b>Connectivity</b>	BT 4.0+HS, Wi-Fi: 802.11b g n USB: microUSB 2.0
<b>Audio</b>	Mic, speakers, 3.5 jack
<b>Built-in devices</b>	GPS, FM
<b>Dimensions</b>	155 x 78 x 8.7 mm
<b>Weight</b>	183g (with battery)
<b>In the box</b>	USB cable, AC charger, screen protective film