

# CAMBLOCK

## 10mm Pitch Standard Profile Rising Clamp Terminal

PCB  
TERMINAL  
BLOCKS

CTB0202

- 2-12 pole interlocking terminal block
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.32-3.3 mm<sup>2</sup> (22-12 AWG)
- Guided pin alignment
- Captive screw



### SPECIFICATION

Rating	10A 300V
Insulation resistance	5000MΩ/1000V
Withstand Voltage	AC1500V/1min
Contact Resistance	20mΩ
Working Temperature	-33°C to +120°C
Mouldings	UL94-V0 flame retardant PA66
Pin/Terminal	Tin plated brass
Wire Clamp	Nickel plated brass
Screw/Torque	M2.5 Steel, Nickel Plated 0.4Nm
Recommended PCB hole size	ø1.5mm

TYPE NO.	POLES	LENGTH
CTB0202/2	2	15.2mm
CTB0202/3	3	25mm
CTB0202/4	4	35mm
CTB0202/5	5	45mm
CTB0202/6	6	55mm
CTB0202/7	7	75mm
CTB0202/8	8	85mm
CTB0202/9	9	95mm
CTB0202/10	10	105mm
CTB0202/11	11	115mm
CTB0202/12	12	125mm

