



### Product Summary

The Omnimax Pro is an omni-directional TV aerial designed for HGV's, trucks and mobile vehicles. With a refreshed look, the original Omnimax has been updated to give even better performance for digital TV reception. Europe's best selling omni-directional aerial just got better.



### Unique and Innovative Features



#### Omni-directional

By receiving signals through 360 degrees, the Omnimax Pro requires no manual directional alignment. Simply re-scan and watch TV.

#### Light and Compact

Occupies minimal roof space, allowing the aerial to be mounted in almost any position.

#### Improved performance

Optimised design for better signal quality.

### Unique and Innovative Features - Continued




#### Variable Signal Booster

1 output and adjustable gain control from 0-18dB allows the user to maximise signal in both high and low signal strength areas.



#### Cable Entry Options

Cable can be routed into the roof directly underneath the aerial or pass along the roof for a flexible entry point.



#### Mounting Options

The Omnimax Pro can be mounted almost anywhere using our range of permanent, semi-permanent and temporary mounts to suit your application (Pole Mount, Magnetic Mount, Suction Mount purchased separately).

### Features

- Receives all available digital terrestrial TV signals without any alignment
- Designed and tested for outdoor use
- High quality, durable and robust construction
- Designed and manufactured in the UK
- 2 year guarantee

### Specifications

<b>Application:</b>	HGV's trucks and vans	<b>Mounting:</b>	Can be mounted using screws and flexible adhesive sealant or the EPDM seal included
<b>Compatibility:</b>	SD, HD, 3D and 4K TV	<b>Housing:</b>	Grey - UV Stable Injection Moulded ABS
<b>Frequency Range:</b>	Wideband for UHF TV (470 - 860 MHz)	<b>Aerial Height:</b>	30cm
<b>Gain:</b>	Up to 18dB with Variable Signal Booster (included)	<b>Aerial Weight:</b>	0.5kg
<b>Power:</b>	12/24V to power Variable Signal Booster		

### Product Contents

- Aerial Head Unit
- Trumpet Base
- 5m Coaxial Cable
- 1m F to Coaxial Flylead
- Variable Signal Booster and Fused Power Lead
- Sealing Gasket
- Fixing Screws
- F Connector Tool
- Instructions

### Product Codes & Variants

B2344/G 12/24V Omnimax Pro - Omni-directional Mobile TV Aerial - Grey


### Packaging Details

<b>Retail Packaging Style:</b>	Art carton
<b>Packaging Dimensions:</b>	(H x W x D): 260 x 210 x 210mm
<b>Packaged Gross weight:</b>	1205g
<b>Barcode Numbers:</b>	B2344/G: 5016163 522544

### Product Approvals and Packaging Symbols



### Product Dimensions



### Kit contents

