

### Important Safety Notice

It is the responsibility of the person installing the electrical equipment to ensure that the installation meets the requirements of the IET wiring regulations and is therefore 'fit for purpose'. Factors such as correct selection of components, cable sizing, protective devices and Earth bonding are all critical and should be checked prior to full testing and power-up. Any other regulations applicable to the equipment being installed such as the Machinery Directive and current health and safety legislation must also be adhered to. All connections (including factory made) must be checked for the correct tightness prior to commissioning of the electrical installation.

All connections should be checked periodically to ensure correct tightness.

**DO NOT USE POWER TOOLS ON THESE PRODUCTS**



	Main Switch (Double Pole)	22 x 58 Fuse Holder
Standards	IEC/EN60947-3	EN60269-1/HD60269-2
Certification/Approvals	Semko, CE	TUV, CE
Current Rating@230V 50Hz	100A	100A Max
Width	2 Module (36mm)	
Utilisation Category	AC-22B	N/A
Terminal Protection	IP20	
Terminal Capacity	35mm <sup>2</sup>	
Recommended Terminal Torque	2.5Nm	

### Dimensions:

#### Technical Data

- IP54 Enclosure
- Amendment 3 Compliant
- Earth and neutral terminals Provided
- Epoxy powder coated RAL 7035

