

PROSAFE MAINS INSPECTION LED LEAD LAMP

PS-ML5

LED

- » 750 Lumen 10w white COB LED
- » Industrial strength polycarbonate
- » Mains cable operated
- » 230v ultra tough 5m cable
- » Hanging hook for easy placement
- » IK07 shockproof
- » Rubberised handle for extra grip
- » Smooth even beam spread
- » Impact resistant to 1m
- » Chemical and corrosion resistant



CONTINUOUS
RUNTIME



20
METRE
BEAM RANGE




750
LUMENS
OUTPUT



IP54
DUST+WATER
RESISTANCE

BATTERY	Mains powered
WEIGHT	2kg
DIMENSION	70 x 450mm



HANGING HOOK FOR EASY
PLACEMENT



RUBBERISED HANDLE
FOR EXTRA GRIP



HIGH POWER COB LED



WIDE BEAM ANGLE

