

HV-RL4

# HIVIS RUBBER WEATHERPROOF LANTERN



BEAMASTER  
Lens®

10  
HOURS  
RUNTIME

250  
METRE  
BEAM RANGE

300  
LUMENS  
OUTPUT


IP54  
DUST & WATER  
RESISTANCE



EASY PUSH BUTTON  
MICRO SWITCH



REAR CHARGING POINT



OPTICAL BEAMMASTER LENS



WEATHERPROOF

- » 300 Lumen white Seoul LED
- » Synthetic industrial grade rubber housing
- » Rear charging point for use with Unillite PS-RB2LION rechargeable battery
- » Floats beam upright in water
- » Ultra tough polycarbonate reflector
- » Optical Beammaster lens for beam penetration
- » Contoured rubber easy grip handle
- » Rubber moulded push micro switch
- » Highly robust build quality
- » IP54 dust and water resistant

**BATTERY** 1 x 6v PJ996 (not included)  
**WEIGHT** 506g (without battery)  
**DIMENSION** 180 x 110 x 125mm