


**Hybrid 4 Channel High Definition DVR Kit with;
2 x Bullet Camera, 500GB (Installed & Formatted)
and Including all Accessories for an Instant Security Solution.**



- Real Time HD Recording and Playback
- Hybrid Channel DVR with Ergonomic Design and Interface
- Hybrid DVR supports High Definition Recording in AHD Analog, IP Technology and CVBS Set Up
- Seamless Set up with P2P Cloud Technology – Fully Network Compatible
- Remotely Access your Security System from Anywhere in the World Via our Free App and Software
- Robust Metal Indoor/Outdoor Security Cameras with 20m IR Providing Clear HD Imaging Day and Night
- Perfect for Home, Retail Unit, Office and Warehouse Applications
- Free Lifetime Technical Support



System	Display Screen	Detailed OSD setup for customization
	Video Standard	PAL (625 lines, 50FPS); NTSC (525 lines, 60FPS)
	Monitor Resolution	VGA, HD, HDMI amongst others
	Encode Capability	4 x 1080N, 7 x 720P, 4 x AHD-L, 2 x 720P (analog), 7 x 720P, 1 x 1080P Approx.
Video	Decode Capability	1 x 1080N
	Motion Detection	Separate channel selection with selected video areas on multiple levels
	Recording Mode	Manual, Alarm, Automatic and Timed
	Local Playback	4 Channel playback with synchronization
	Video Search	Time, date, event and channel search
Record	Data Occupation	720P 20Gb/Day, 960H 12 - 20G/day per channel plus audio
	Video Storage	Local HDD/SSD or Network
	Backup Mode	Network Backup, USB portable HDD/SDD backup if required
	Video Input	4 Channel BNC
	Video Output	1 Channel VGA, 1 Channel HDMI
Interfaces	Audio Input	4 Channel
	Audio Output	1 Channel
	Alarm Input	n/a
	Alarm Output	n/a
	Network Port	Ethernet 10/100Mbps auto-sensing
	PTZ Control	Dependent of model of camera connected
	USB port	USB2.0 standard compatibility
	Power	Standard, regional compatible power input





Image Sensor	1/4" OV 1.0MP CMOS Sensor
Effective PictureElements	1280 X720
Resolution	720P
Signal System	PAL / NTSC
Minimum Illumination	0.01 Lux/F1.2
S/N Ratio	More than 50dB
Synchronous System	Internal,Negative sync.
IR Distance	20 Meters (with ϕ 5X42PCS Infrared LED)
IR Power On	Photodiode AUTO Control
Video Output	AHD/CVI/CVBS/TVI
Functions	DNR, OSD
Power/Current	DC12V(+/-10%)/500mA
Lens	Board Len 3.6mm
Weather Proof	IP66
Dimension (mm)	151(W) x 64(H) x 65.5(D)
Weight (g)	700
Operating Conditions	-10~+50oC RH95% MAX

Kit Contents:

- HD Hybrid 4 Channel with 500GB HDD Installed & Formatted
- 2 x 720p/960h White Metal Bullet Camera With IR
- 2 x 18m BNC Shotgun Cable
- 1 x 5-Way Power Splitter
- 1 x Power supply
- 1 x Manual
- 1 x Mouse
- 1 x Remote Control
- 1 x Lifetime Technical Support



Images shown are simulated,
for illustrative purposes