


SMB Buccaneer®



IP68




- Sealed to IP68 when mated
- 50Ω Impedance SMB connector
- Frequency range 0-4GHz
- Contact resistance
 - centre - 6mΩ max.
 - outer - 2.5mΩ max.
- Gold plated contacts
- Diameter over coupling ring 19mm
- Body moulding, Nylon UL94-V0 rated
- Two versions of Flex Connector
 - re-wireable
 - pre-wired - lengths 1m, 3m & 5m
- Panel connector
 - pre-wired - lengths 0.5m, 1m & 1.5m
- Cable accommodation (flex re-wireable), RG-174
- Cable type (pre-wired connectors), RG-174

RE-WIREABLE FLEX CONNECTOR



PX0415/1

- Mates with Panel connector (PX0414)
- Re-wireable connector
- For RG-174 cable
- Supplied with SMB plug




Part no.	Description
PX0415/1	Re-wireable connector with SMB Plug - for RG-174 cable

PRE-WIRED FLEX CONNECTOR



PX0416/xMxx

- Mates with Panel connector (PX0414)
- Pre-wired
- Supplied with SMB plug terminated with RG-174 cable
- 1m, 3m & 5m cable lengths




Part no.	Description
PX0416/1M00	Pre-wired connector with SMB plug - cable length 1m
PX0416/3M00	Pre-wired connector with SMB plug - cable length 3m
PX0416/5M00	Pre-wired connector with SMB plug - cable length 5m

PANEL MOUNTING CONNECTOR



PX0414/xMxx

- Mates with Flex connectors (PX0415, PX0416)
- Single hole fixing
- Supplied with SMB jack terminated with RG-174 cable



Part no.	Description
PX0414/0M50	Panel connector with SMB jack - cable length 0.5m
PX0414/1M00	Panel connector with SMB jack - cable length 1m
PX0414/1M50	Panel connector with SMB jack - cable length 1.5m

SEALING CAPS AND ACCESSORIES



Part no.	Description
PX0480	Sealing cap for PX0415/PX0416 flex connectors
PX0481	Sealing cap for PX0414 chassis connector
14319	Hand crimp tool for SMB