


US Power Supply Cord with IEC Connector C13, hospital grade



**Description**

- 1 Function :
- Power Cord , Protection class I
- Pin temperature 70 °C
- Hospital grade
- custom specific versions on request

**References**

Alternative: Standard version

**Technical Data**

Ratings UL/CSA	10A / 125VAC; 50/60Hz	appliance inlet/-outlet	C13 acc. to IEC 60320-1
Allowable Operation Temperature	-40 °C to 70 °C		UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I
IP-Protection	from front side IP 40 acc. to IEC 60529		
Insulation cover	Suitable for appliances with protection class I acc. to IEC 61140		
Material: Housing	PVC, Transparent		

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

**All Variants**

Connector		cable				Plug					Order Number
Type	V-Lock	Cord Type	Conductor cross section	Length [m]	Color	Type	Country	Standard	Style	Index	
C13		SJT 3x18 AWG	3 x 18 AWG	3.0	Transparent	North America	USA	NEMA 5-15	straight	-	4300.0920

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging unit** 50 Pcs