

Touch-Safe Fuseholder, 35 mm DIN-Rail, 10.3 x 38 mm, 1000 VDC



1000 VDC · 4 W · 600VAC/DC · 30 A (UL/CSA)



Description

- Mountable on 35 mm DIN-Rail
- Easy installation and removal of fuses
- For Fuses up to 100 kA Interrupting Rating

Standards

- IEC 60269-2, -4, -6
- UL 4248-1
- CSA C22.2 no. 39

Approvals

- Approval Reference Type: FSO
- UL File Number: E39328
- CSA File Number: 248899

Applications

- Combiner Boxes in Photovoltaic Systems

References

Fuseholder to [ASO 10.3x38](#)

Weblinks


[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Fuse-Link	10.3 x 38 mm
Mounting	DIN-Rail Mounting
Terminal	Press plate: 2 - 10 mm ² / AWG #8 - 14 (stranded), 2 - 6 mm ² , AWG #10 - 14 (solid), 2 Nm / 17.7 lb-in (max. torque)
Rated Voltage	1000VDC (Self certified), 600VAC/DC (UL/CSA)
Rated current	30A (UL/CSA)
Rated Power Acceptance IEC	4 W max. 4 W (self certified)
Degree of Protection	IP 20
Admissible Ambient Air Temp.	-40°C to 130°C
Material: Socket	Thermoplastic, UL 94V-0
Unit Weight	54 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	Type, Tech. Information

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

Dimension



Do not open under load

All Variants

Holder	Remark	Order Number
●	1-pole	0091.0001
●	2-pole	0091.0002
●	3-pole	0091.0003
●	4-pole	0091.0004

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging Unit	Order Number	Quantity
	0091.0001	Bulk (10 pcs.)
	0091.0002	Bulk (5 pcs.)
	0091.0003	Bulk (4 pcs.)
	0091.0004	Bulk (3 pcs.)