

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to IEC-320-C20) 10-ft.

MODEL NUMBER: P036-010



Highlights

- C19 to C20 Power Cord, 10 ft.
- 12AWG x 3C, 20 Amp Rated
- RoHS Approved

Package Includes

- C19 to C20 Power Cord, 10 ft.

Description

Use Tripp Lite's P036-010 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20AMP rated, 250V - ideal for use with Blade Server Chassis.

Features

- Molded, Heavy-Duty Power Cord, 10 ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Approved

Specifications

| INPUT | |
|----------------------|-------------|
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.1 |
| PHYSICAL | |
| Color | Black |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C20 |
| Side B - Connector 1 | IEC-320-C19 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| WARRANTY | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>