


Tools and Dies

TBM6S Crimp Tool



Creates diamond-style crimp



- Wide ranges of #8 AWG thru 500 kcmil for copper lugs, splices and taps and #10 AWG thru 350 kcmil for aluminum lugs and splices
- Also installs 63105 through 63140 orange, green and blue H-taps
- Shure-Stake® mechanism ensures a properly completed crimp each time
- Comes complete with plastic carrying case and wire brush

Note: The TBM6S tool can also be used to crimp Sta-Kon® terminals. See Sta-Kon® section for dies.

CAT. NO.	COLOR CODE	CAT. NO UPPER DIE	CAT. NO LOWER DIE	PKG. QTY.
TBM6S	RED	13475	13477	1
	BLUE	13475	13477	
	GRAY	13472	13476	
	BROWN	13474	13477	
	GREEN	13474	13477	
	PINK	13475	13477	
	BLACK	13474	13477	
	ORANGE	13474	13477	
	PURPLE	13475	13477	
	YELLOW	13473	13476	
	GOLD	13474	13477	
	TAN	13475	13477	
	OLIVE	13475	13477	
	RUBY	13473	13476	
	WHITE	13473	13476	
	RED	13472	13476	
	BLUE	13472	13476	
BROWN	13478	13478		

Carrying Cases for TBM5S and TBM6S

CAT. NO.	DESCRIPTION	PKG. QTY.
295-31365M	Steel Carrying Case for TBM5S and TBM6S	1
295-31365	Plastic Carrying Case for TBM5S and TBM6S	1

TBM8S Crimp Tool



Creates diamond-style crimp



- Installs code copper lugs and connectors #8 AWG through 500 kcmil
- Installs aluminum lugs and connectors #10 AWG through 350 kcmil
- Shure-Stake® mechanism ensures positive compression
- Included dies are color coded and provide die-code embossing for easy installation and inspection
- Installs all code copper compression joints and small C-taps
- Comes complete with installing dies and wire brush in plastic carrying case

CAT. NO.	COLOR CODE	DIE CAT. NO	PKG. QTY.
TBM8S	RED	13461	1
	BLUE		
	GRAY		
	BROWN	13462	
	GREEN		
	PINK		
	BLACK	13463	
	ORANGE		
	PURPLE		
	YELLOW	13464	
	GOLD		
	TAN		
	OLIVE	13465	
	RUBY		
	WHITE	13465	
	RED	13466	
	BLUE	13467	
BROWN	13468		