



Flexible Cable Support

Heladuct Flex

Heladuct flexible cable supports are commonly used in switching cabinets. They are also used in the furniture industry, where cables need to be routed rapidly and attractively.

Features and Benefits

- Space-saving wiring system
- Highly flexible, can be installed at angles of 90° and higher
- Cable clearly open to view
- Rapid mounting with screws or adhesive strip with high-quality foam bonding layer



Heladuct Flex- clearly and space-saving arrangement of wiring, even at angles above 90°.

MATERIAL	Polypropylene (PP)
Operating Temperature	-20 °C to +70 °C
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL94 V0 (excluding adhesive)



TYPE	Nominal Ø	No. of Wires			Max. load on a length of 500 mm at 70 °C (g)	Colour	Length (L)	Article-No.
		9 x 0.75 mm ²	6 x 1.50 mm ²	4 x 2.50 mm ²				
Heladuct Flex10	10	9 x 0.75 mm ²	6 x 1.50 mm ²	4 x 2.50 mm ²	100	White (WH)	500.0	164-11008
Heladuct Flex20	20	32 x 0.75 mm ²	22 x 1.50 mm ²	14 x 2.50 mm ²	300	White (WH)	500.0	164-21008
Heladuct Flex30	30	67 x 0.75 mm ²	50 x 1.50 mm ²	34 x 2.50 mm ²	650	White (WH)	500.0	164-31008
Heladuct Flex40	40	-	81 x 1.50 mm ²	60 x 2.50 mm ²	1,100	White (WH)	500.0	164-41008

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

Heladuct Flex with Adhesive

TYPE	Nominal Ø	No. of Wires			Max. load on a length of 500 mm at 70 °C (g)	Colour	Length (L)	Article-No.
		9 x 0.75 mm ²	6 x 1.50 mm ²	4 x 2.50 mm ²				
Heladuct Flex10SK	10	9 x 0.75 mm ²	6 x 1.50 mm ²	4 x 2.50 mm ²	100	White (WH)	500.0	164-11108
Heladuct Flex20SK	20	32 x 0.75 mm ²	22 x 1.50 mm ²	14 x 2.50 mm ²	300	White (WH)	500.0	164-21108
Heladuct Flex30SK	30	67 x 0.75 mm ²	50 x 1.50 mm ²	34 x 2.50 mm ²	500	White (WH)	500.0	164-31108
Heladuct Flex40SK	40	-	81 x 1.50 mm ²	60 x 2.50 mm ²	400	White (WH)	500.0	164-41108

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.