

EAO – Your Expert Partner for Human Machine Interfaces

82-6153.22A4 - Illuminated pushbutton 22 mm stainless-steel, maintain

82-6153.22A4 - Illuminated pushbutton 22 mm stainless-steel, maintain



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out Ø 22,3 mm
Design flush

Front

Front dimension Ø 25 mm
Front shape round
Front ring shape flush
Front bezel material Stainless steel

Other Attributes

Operating voltage 24 V VDC
Weight 0,018 kg
Operation current 7 mA

Operating-/Indication part

Lens optics opaque
Lens material Stainless steel
Lens profile flat
Lens illumination illuminative
Lens colour Stainless steel

IP-Rating

Front protection IP 65, IP 67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Maintained

Switching element

Switching current 3 A
Contact material gold-plated silver
Contacts 1 C
Switching system Snap-action switching element
Switching voltage 240 V VAC/DC

Illumination

Illumination Dot with LED bi-colour red/green


Function

Illuminated pushbutton

EAO – Your Expert Partner for Human Machine Interfaces

82-6153.22A4 - Illuminated pushbutton 22 mm stainless-steel, maintain


Dimensions



Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: C = Maintained

Contacts: C = Changeover