

FEX FEX 2819 13 T



Sample photo

Order symbol: FEX 2819 13 T
Product nbr: 4120801
Description: Enclosure, PC
Remarks: Ex e II, EN 60079; IK 4J

EAN: 6418074007902
EI. number:
 Finland: 3424642
 Electric No. Denmark: 8212026353
 Electric No. Italy: 7801020
 Electric No. Sweden: 4120801

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	278	188	130	EKJVT	Mounting plate
inch:	10.9	7.4	5.1	EKMVT	Mounting plate
Materials:				EKOVT	Mounting plate
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Polyamide				
Cover colour:	Clear transparent				
Cover screws colour:	Grey				
Gasket material:	Silicone				
Temperatures:					
Temperature °C (short term):	-40 ... 120 °C				
Temperature °C (continuous):	-10 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	14 ... 175 °F				
Accessories:				EKPVT	Mounting plate
				EKTVT	Mounting plate
				EKUVT	Mounting plate
				EKV 12	DIN-35 Mounting rail
				EKV 22	DIN-35 Mounting rail
				EKV 32	DIN-35 Mounting rail
Rating:					
				Ingress Protection (EN 60529): IP54	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				Impact Resistance (EN 50014): 4J	
Certificates:					
				ATEX	
				Attestation of Conformity	
				EKHVT	
				Mounting plate	

