

**FEX FEX 3828 18 T**



Sample photo

**Order symbol:** FEX 3828 18 T  
**Product nbr:** 4120814  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074008046  
**EI. number:**  
 Finland: 3424665  
 Electric No. Denmark: 8212026492  
 Electric No. Italy: 7801055  
 Electric No. Sweden: 4120814

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	378	278	180	EKJVT	Mounting plate
inch:	14.9	10.9	7.1	EKMVT	Mounting plate
Materials:			EKOVT	Mounting plate	
<b>Material:</b>	Polycarbonate		EKPVT	Mounting plate	
<b>Base colour:</b>	RAL 7035 -light grey		EKTVT	Mounting plate	
<b>Cover screws material:</b>	Polyamide		EKUVT	Mounting plate	
<b>Cover colour:</b>	Clear transparent		EKV 12	DIN-35 Mounting rail	
<b>Cover screws colour:</b>	Grey		EKV 22	DIN-35 Mounting rail	
<b>Gasket material:</b>	Silicone		EKV 32	DIN-35 Mounting rail	
Temperatures:			Rating:		
<b>Temperature °C (short term):</b>	-40 ... 120 °C		Ingress Protection (EN 60529): IP54		
<b>Temperature °C (continuous):</b>	-10 ... 80 °C		Electrical insulation: Totally insulated		
<b>Temperature °F (short term):</b>	-40 ... 250 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Temperature °F (continuous):</b>	14 ... 175 °F		Impact Resistance (EN 50014): 4J		
Accessories:			Certificates:		
EKHVT	Mounting plate		ATEX		
			Attestation of Conformity		

