

CARDMASTER PC 17/16-3



Sample photo

Order symbol: PC 17/16-3
Product nbr: 7525165
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056726
El. number:
 Finland: 3438230
 Electric No. 8212016648
 Denmark:
 Electric No. Sweden: 2537302

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:			Accessories:		
Length	Width	Height	FP 17/16	Front plate (aluminium)	
mm:	166	160	134	FC PC 17/16	Frame of PC front plate
inch:	6.5	6.3	5.3		

Materials:		Rating:	
Material:	Polycarbonate	Ingress Protection (EN 60529):	IP65
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262):	IK07/IK08
Cover colour:	Smoked grey	Electrical insulation:	Totally insulated
Gasket material:	EPDM & PUR	Halogen free (DIN/VDE 0472, Part 815):	1
		UV resistance:	UL 508
		Flammability Rating:	UL 746C 5"
		Glow Wire Test (IEC 695-2-1) °C:	960
		NEMA Class:	NEMA 1, 3, 3R, 4, 4X, 12, 13

Temperatures:		Certificates:	
Temperature °C (short term):	-40 ... 120 °C	SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C	Gost R	
Temperature °F (short term):	-40 ... 250 °F		
Temperature °F (continuous):	-40 ... 175 °F		

Accessories:	
MP 17/16	Mounting plate

