

**CAB CAB PC 504020 G**



Sample photo

**Order symbol:** CAB PC 504020 G  
**Product nbr:** 8113360  
**Description:** Cabinet, PC  
**Remarks:** Latches on the long side

**EAN:** 6418074020321  
**EI. number:**  
 Finland: 3424120  
 Electric No. 8212020265  
 Denmark:  
 Electric No. Italy: 7821055  
 Electric No. Sweden: 2539977

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			Accessories:		
	Length	Width	Height		
<b>mm:</b>	500	400	200	EKIV 37	DIN-35 Mounting rail
<b>inch:</b>	19.7	15.7	7.9	DS35370E1	DIN-35 Mounting rail
<b>Materials:</b>			EKIV 47	DIN-35 Mounting rail	
<b>Material:</b>	Polycarbonate		DS35470E1	DIN-35 Mounting rail	
<b>Base colour:</b>	RAL 7035 -light grey		FP A 54	Swing-out door/Front plate	
<b>Cover colour:</b>	RAL 7035 -light grey		MB 12225 AL	Swing door set	
<b>Gasket material:</b>	Polyurethane		FP 54	Front plate	
<b>Temperatures:</b>			FP 18X2-54	Front plate	
<b>Temperature °C (short term):</b>	-40 ... 120 °C		DRF 54	DIN rail frame set	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C		<b>Rating:</b>		
<b>Temperature °F (short term):</b>	-40 ... 250 °F		Ingress Protection (EN 60529): IP65		
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		Impact Resistance (EN 62262): IK08		
<b>Accessories:</b>			Electrical insulation: Totally insulated		
EKIV 54	Mounting plate		Halogen free (DIN/VDE 0472, Part 815): 1		
			UV resistance: UL 508		
			Flammability Rating: UL 746C 5"		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			<b>Certificates:</b>		
			Germanischer Lloyd (GL)		
			SGS Fimko		
			Lloyds Register of Shipping (LR)		
			Gost R		

