

**CAB CAB ABS 302018 G**



Sample photo

**Order symbol:** CAB ABS 302018 G  
**Product nbr:** 8183330  
**Description:** Cabinet, ABS, Grey door  
**Remarks:** Latches on the long side

**EAN:** 6418074020062  
**EI. number:**  
 Finland: 3424301  
 Electric No. 8212020508  
 Denmark:  
 Electric No. Italy: 7811015  
 Electric No. Sweden: 2540061

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Accessories:		
mm:		300	200	180	EKIV 17	DIN-35 Mounting rail	
inch:		11.8	7.9	7.1	DS35170E1	DIN-35 Mounting rail	
<b>Materials:</b>						EKIV 27	DIN-35 Mounting rail
<b>Material:</b>	ABS					DS35270E1	DIN-35 Mounting rail
<b>Base colour:</b>	RAL 7035 -light grey					FP A 23	Swing-out door/Front plate
<b>Cover colour:</b>	RAL 7035 -light grey					MB 12225 AL	Swing door set
<b>Gasket material:</b>	Polyurethane					FP 23	Front plate
<b>Temperatures:</b>						FP 12-23	Front plate
<b>Temperature °C (short term):</b>	-40 ... 80 °C					DRF 23	DIN rail frame set
<b>Temperature °C (continuous):</b>	-40 ... 60 °C					<b>Rating:</b>	
<b>Temperature °F (short term):</b>	-40 ... 175 °F					Ingress Protection (EN 60529): IP65	
<b>Temperature °F (continuous):</b>	-40 ... 140 °F					Impact Resistance (EN 62262): IK08	
<b>Accessories:</b>						Electrical insulation: Totally insulated	
EKIV 23	Mounting plate					Halogen free (DIN/VDE 0472, Part 815): 1	
						Flammability Rating: UL 94 HB	
						Glow Wire Test (IEC 695-2-1) °C: 650	
						NEMA Class: NEMA 1, 4, 4X, 12, 13	
						<b>Certificates:</b>	
						SGS Fimko	
						Gost R	

