

CAB CAB ABS 303018 G



Sample photo

Order symbol: CAB ABS 303018 G
Product nbr: 8183340
Description: Cabinet, ABS, Grey door
Remarks: Latches on the long side

EAN: 6418074020161
EI. number:
 Finland: 3424307
 Electric No. Denmark: 8212020524
 Electric No. Italy: 7811025
 Electric No. Sweden: 2540067

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	300	300	180	EKIV 27 DIN-35 Mounting rail
inch:	11.8	11.8	7.1	DS35270E1 DIN-35 Mounting rail

Materials:	Accessories:
Material: ABS	MB 12225 AL Swing door set
Base colour: RAL 7035 -light grey	FP 33 Front plate
Cover colour: RAL 7035 -light grey	FP 12-33 Front plate
Gasket material: Polyurethane	FP 12x2-33 Front plate
	DRF 33 DIN rail frame set

Temperatures:	Rating:
Temperature °C (short term): -40 ... 80 °C	Ingress Protection (EN 60529): IP65
Temperature °C (continuous): -40 ... 60 °C	Impact Resistance (EN 62262): IK08
Temperature °F (short term): -40 ... 175 °F	Electrical insulation: Totally insulated
Temperature °F (continuous): -40 ... 140 °F	Halogen free (DIN/VDE 0472, Part 815): 1
	Flammability Rating: UL 94 HB
	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4, 4X, 12, 13

Accessories:	Certificates:
EKIV 33 Mounting plate	SGS Fimko Gost R

