

**CAB CAB ABS 302018 T**



Sample photo

**Order symbol:** CAB ABS 302018 T  
**Product nbr:** 8183030  
**Description:** Cabinet, ABS  
**Remarks:** Latches on the long side

**EAN:** 6418074020079  
**EI. number:**  
 Finland: 3424351  
 Electric No. 8212020511  
 Denmark:  
 Electric No. Italy: 7812015  
 Electric No. Sweden: 2540031

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions:                         |  | Length               | Width | Height | Accessories:                             |                            |
|-------------------------------------|--|----------------------|-------|--------|--|----------------------------|
| mm:                                 |  | 300                  | 200   | 180    | EKIV 17                                  | DIN-35 Mounting rail       |
| inch:                               |  | 11.8                 | 7.9   | 7.1    | DS35170E1                                | DIN-35 Mounting rail       |
| <b>Materials:</b>                   |  |                      |       |        | EKIV 27                                  | DIN-35 Mounting rail       |
| <b>Material:</b>                    |  | ABS                  |       |        | DS35270E1                                | DIN-35 Mounting rail       |
| <b>Base colour:</b>                 |  | RAL 7035 -light grey |       |        | FP A 23                                  | Swing-out door/Front plate |
| <b>Cover colour:</b>                |  | Smoked grey          |       |        | MB 12225 AL                              | Swing door set             |
| <b>Gasket material:</b>             |  | Polyurethane         |       |        | FP 23                                    | Front plate                |
| <b>Temperatures:</b>                |  |                      |       |        | FP 12-23                                 | Front plate                |
| <b>Temperature °C (short term):</b> |  | -40 ... 80 °C        |       |        | DRF 23                                   | DIN rail frame set         |
| <b>Temperature °C (continuous):</b> |  | -40 ... 60 °C        |       |        | <b>Rating:</b>                           |                            |
| <b>Temperature °F (short term):</b> |  | -40 ... 175 °F       |       |        | Ingress Protection (EN 60529): IP65      |                            |
| <b>Temperature °F (continuous):</b> |  | -40 ... 140 °F       |       |        | Impact Resistance (EN 62262): IK08       |                            |
| <b>Accessories:</b>                 |  |                      |       |        | Electrical insulation: Totally insulated |                            |
| EKIV 23                             |  | Mounting plate       |       |        | Halogen free (DIN/VDE 0472, Part 815): 1 |                            |
|                                     |  |                      |       |        | Flammability Rating: UL 94 HB            |                            |
|                                     |  |                      |       |        | Glow Wire Test (IEC 695-2-1) °C: 650     |                            |
|                                     |  |                      |       |        | NEMA Class: NEMA 1, 4, 4X, 12, 13        |                            |
|                                     |  |                      |       |        | <b>Certificates:</b>                     |                            |
|                                     |  |                      |       |        | SGS Fimko                                |                            |
|                                     |  |                      |       |        | Gost R                                   |                            |

