

CAB CAB ABS 504020 T



Sample photo

Order symbol: CAB ABS 504020 T
Product nbr: 8183060
Description: Cabinet, ABS
Remarks: Latches on the long side

EAN: 6418074020390
EI. number:
 Finland: 3424370
 Electric No. 8212020579
 Denmark:
 Electric No. Italy: 7812055
 Electric No. Sweden: 2540047

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	500	400	200	EKIV 37 DIN-35 Mounting rail
inch:	19.7	15.7	7.9	DS35370E1 DIN-35 Mounting rail

Materials:	Accessories:
Material: ABS	EKIV 47 DIN-35 Mounting rail
Base colour: RAL 7035 -light grey	DS35470E1 DIN-35 Mounting rail
Cover colour: Smoked grey	FP A 54 Swing-out door/Front plate
Gasket material: Polyurethane	MB 12225 AL Swing door set
	FP 54 Front plate
	FP 18X2-54 Front plate
	DRF 54 DIN rail frame set

Temperatures:	Rating:
Temperature °C (short term): -40 ... 80 °C	Ingress Protection (EN 60529): IP65
Temperature °C (continuous): -40 ... 60 °C	Impact Resistance (EN 62262): IK08
Temperature °F (short term): -40 ... 175 °F	Electrical insulation: Totally insulated
Temperature °F (continuous): -40 ... 140 °F	Halogen free (DIN/VDE 0472, Part 815): 1
	Flammability Rating: UL 94 HB
	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4, 4X, 12, 13

Accessories:
EKIV 54 Mounting plate

Certificates:
SGS Fimko
Gost R

