

**CAB CAB PC 504020 T3B**



Sample photo

**Order symbol:** CAB PC 504020 T3B  
**Product nbr:** 8113062  
**Description:** Cabinet, PC  
**Remarks:** Locks on the long side

**EAN:** 6418074020376  
**EI. number:**  
 Finland: 3424174  
 Electric No. Denmark: 8212019276  
 Electric No. Italy: 7822060  
 Electric No. Sweden: 2539955

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	500	400	200	EKIV 37	DIN-35 Mounting rail
<b>inch:</b>	19.7	15.7	7.9	DS35370E1	DIN-35 Mounting rail
<b>Materials:</b>				EKIV 47	DIN-35 Mounting rail
<b>Material:</b>	Polycarbonate			DS35470E1	DIN-35 Mounting rail
<b>Base colour:</b>	RAL 7035 -light grey			FP A 54	Swing-out door/Front plate
<b>Cover colour:</b>	Smoked grey			MB 12225 AL	Swing door set
<b>Gasket material:</b>	Polyurethane			FP 54	Front plate
<b>Temperatures:</b>				FP 18X2-54	Front plate
<b>Temperature °C (short term):</b>	-40 ... 120 °C			DRF 54	DIN rail frame set
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			<b>Rating:</b>	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Ingress Protection (EN 60529): IP65	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Impact Resistance (EN 62262): IK08	
<b>Accessories:</b>				Electrical insulation: Totally insulated	
EKIV 54	Mounting plate			Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				<b>Certificates:</b>	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Lloyds Register of Shipping (LR)	
				Gost R	

