


MNX PC 175/125 HT



Sample photo

Order symbol: PC 175/125 HT
Product nbr: 6011922
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074052209
EI. number:
 Finland: 3435204
 Electric No. Denmark: 8212027666
 Electric No. Sweden: 6011922

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions: | | | | Accessories: | |
|-------------------------------------|-----------------------------------|-------|--------|--|----------------------------|
| | Length | Width | Height | | |
| mm: | 180 | 180 | 125 | MIN 15 | DIN-15 Mounting rail |
| inch: | 7.1 | 7.1 | 4.9 | MIV 15 | DIN-35 Mounting rail |
| Materials: | | | | FP A 175/180 | Front plate (Aluminium) |
| Material: | Polycarbonate | | | HFP 180 | Front plate hinge series |
| Base colour: | RAL 7035 -light grey | | | FP 22046 | Wall fastening lug (4 pcs) |
| Cover screws material: | Polyamide | | | Rating: | |
| Cover colour: | Smoked grey | | | Ingress Protection (EN 60529): IP66/IP67 | |
| Cover screws colour: | Black | | | Impact Resistance (EN 62262): IK08 | |
| Gasket material: | TPE | | | Electrical insulation: Totally insulated | |
| Temperatures: | | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| Temperature °C (short term): | -40 ... 120 °C | | | UV resistance: UL 508 | |
| Temperature °C (continuous): | -40 ... 80 °C | | | Flammability Rating: UL 746C 5" | |
| Temperature °F (short term): | -40 ... 250 °F | | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| Temperature °F (continuous): | -40 ... 175 °F | | | NEMA Class: NEMA 1, 4, 4X, 6, 12, 13 | |
| Accessories: | | | | Certificates: | |
| MIV 175 | Mounting plate (Galvanized steel) | | | Germanischer Lloyd (GL) | |
| | | | | SGS Fimko | |
| | | | | Gost R | |

