

MNX PC 200/125 XHT



Sample photo

Order symbol: PC 200/125 XHT
Product nbr: 6013927
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074021946
EI. number:
 Finland: 3421686
 Electric No. Denmark: 8212022661
 Electric No. Italy: 7352150
 Electric No. Sweden: 6013927

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	255	180	125	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	4.9	MIN 20	DIN-15 Mounting rail
				MIV 15	DIN-35 Mounting rail
				MIV 20	DIN-35 Mounting rail
				FP A 200/180	Front plate (Aluminium)
				HFP 180	Front plate hinge series
				FP 22046	Wall fastening lug (4 pcs)
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	Smoked grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Black			UV resistance: UL 508	
Gasket material:	Polyurethane			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			Germanischer Lloyd (GL)	
Temperature °C (continuous):	-40 ... 80 °C			SGS Fimko	
Temperature °F (short term):	-40 ... 250 °F			Gost R	
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MIV 200	Mounting plate (Galvanized steel)				

