

MNX PC 300/150 ZT



Sample photo

Order symbol: PC 300/150 ZT
Product nbr: 6017938
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074061522
EI. number:
 Finland: 3435626
 Electric No. Denmark: 8212027996
 Electric No. Sweden: 6017938

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	360	255	152	MIV 200 Mounting plate (Galvanized steel)
inch:	14.2	10.0	6.0	MIV 150 Mounting plate (Galvanized steel)

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: Smoked grey
Cover screws colour: Black
Gasket material: Polyurethane

Accessories:

MIV 200 Mounting plate (Galvanized steel)
 MIV 150 Mounting plate (Galvanized steel)
 MIN 20 DIN-15 Mounting rail
 MIN 15 DIN-15 Mounting rail
 MIV 30 DIN-35 Mounting rail
 MIV 20 DIN-35 Mounting rail
 MIV 15 DIN-35 Mounting rail
 FP 10674

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 4, 4X and 6

Accessories:

MIV 300 Mounting plate (Galvanized steel)

