



Order symbol: TA131007
Product nbr: 5814040
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011480
EI. number:
 Finland: 3438269
 Electric No. Denmark: 8212045237
 Electric No. Sweden: 5814040

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	130	95	65	MP 1310 Mounting plate
inch:	5.1	3.7	2.6	FP 10674 DPS 14553 Grey sealing plug set
Materials:	Material: ABS			Rating:
	Base colour: RAL 7035 -light grey			Ingress Protection (EN 60529): IP65
	Cover screws material: Polyamide			Impact Resistance (EN 62262): IK07
	Cover colour: RAL 7035 -light grey			Electrical insulation: Totally insulated
	Cover screws colour: Grey			Halogen free (DIN/VDE 0472, Part 815): 1
	Gasket material: Polyurethane			Flammability Rating: UL 94 HB
				Glow Wire Test (IEC 695-2-1) °C: 650
Temperatures:	Temperature °C (short term): -40 ... 80 °C			Certificates:
	Temperature °C (continuous): -40 ... 60 °C			SGS Fimko
	Temperature °F (short term): -40 ... 175 °F			
	Temperature °F (continuous): -40 ... 140 °F			
Accessories:	DRM 100 DIN-15 Mounting rail			

