



Order symbol: TA191209T
Product nbr: 5814005
Description: Enclosure, ABS
Remarks: Clear transparent cover

EAN: 6418074060778
EI. number:
 Finland: 3435692
 Electric No. Denmark: 8212035014
 Electric No. Sweden: 5814005

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	187	122	90	MIV 10 DIN-35 Mounting rail
inch:	7.4	4.8	3.5	DH-3 DIN-35 Mounting rail
Materials:				FP 10674 DPS 14553 Grey sealing plug set
Material:	ABS			Rating:
Base colour:	RAL 7035 -light grey			Ingress Protection (EN 60529): IP65
Cover screws material:	Polyamide			Impact Resistance (EN 62262): IK07
Cover colour:	Clear transparent			Electrical insulation: Totally insulated
Cover screws colour:	Grey			Halogen free (DIN/VDE 0472, Part 815): 1
Gasket material:	Polyurethane			Flammability Rating: UL 94 HB
Temperatures:				Glow Wire Test (IEC 695-2-1) °C: 650
Temperature °C (short term):	-40 ... 80 °C			Certificates:
Temperature °C (continuous):	-40 ... 60 °C			SGS Fimko
Temperature °F (short term):	-40 ... 175 °F			
Temperature °F (continuous):	-40 ... 140 °F			
Accessories:				
MP 1912	Mounting plate			

