

TEMPO TA241911T



Order symbol: TA241911T
Product nbr: 5814007
Description: Enclosure, ABS
Remarks: Clear transparent cover

EAN: 6418074060792
EI. number:
 Finland: 3435696
 Electric No. Denmark: 8212035056
 Electric No. Sweden: 5814007

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	240	191	107	EKV 12 DIN-35 Mounting rail
inch:	9.4	7.5	4.2	DR 210 DIN-35 Mounting rail
				FP 10674

Materials:		
DPS 14553		Grey sealing plug set

Material:	ABS
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Clear transparent
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:
Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
Flammability Rating: UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650

Temperatures:
Temperature °C (short term): -40 ... 80 °C
Temperature °C (continuous): -40 ... 60 °C
Temperature °F (short term): -40 ... 175 °F
Temperature °F (continuous): -40 ... 140 °F

Certificates:
SGS Fimko

Accessories:
MP 2419 Mounting plate

