



**Order symbol:** TAM111107  
**Product nbr:** 5814021  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074011435  
**EI. number:**  
 Finland: 3438264  
 Electric No. Denmark: 8212045266  
 Electric No. Sweden: 5814021

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:	
mm:	110	110	65	DRM 80	DIN-15 Mounting rail
inch:	4.3	4.3	2.6	FP 10674	
				DPS 14553	Grey sealing plug set

Materials:		Rating:	
<b>Material:</b>	ABS	<b>Ingress Protection (EN 60529):</b>	IP65
<b>Base colour:</b>	RAL 7035 -light grey	<b>Impact Resistance (EN 62262):</b>	IK07
<b>Cover screws material:</b>	Polyamide	<b>Electrical insulation:</b>	Totally insulated
<b>Cover colour:</b>	RAL 7035 -light grey	<b>Halogen free (DIN/VDE 0472, Part 815):</b>	1
<b>Cover screws colour:</b>	Grey	<b>Flammability Rating:</b>	UL 94 HB
<b>Gasket material:</b>	Polyurethane	<b>Glow Wire Test (IEC 695-2-1) °C:</b>	650

Temperatures:		Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 80 °C	SGS Fimko	
<b>Temperature °C (continuous):</b>	-40 ... 60 °C		
<b>Temperature °F (short term):</b>	-40 ... 175 °F		
<b>Temperature °F (continuous):</b>	-40 ... 140 °F		

Accessories:	
MP 1111	Mounting plate

