

TEMPO TAM201610



Sample photo

Order symbol: TAM201610
Product nbr: 5814025
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074062673
EI. number:
Finland: 3438006
Electric No. Sweden: 5814025

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Dimensions:		Length	Width	Height	Accessories:	
mm:		201	163	98	DH-3	DIN-35 Mounting rail
inch:		7.9	6.4	3.9	ARH 2320	DIN-35 Mounting rail
Materials:					FP 10674	
Material:	ABS			DPS 14553	Grey sealing plug set	
Base colour:	RAL 7035 -light grey			Rating:		
Cover screws material:	Polyamide			Ingress Protection (EN 60529): IP65		
Cover colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07		
Cover screws colour:	Grey			Electrical insulation: Totally insulated		
Gasket material:	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1		
Temperatures:					Certificates:	
Temperature °C (short term):	-40 ... 80 °C			SGS Fimko		
Temperature °C (continuous):	-40 ... 60 °C					
Temperature °F (short term):	-40 ... 175 °F					
Temperature °F (continuous):	-40 ... 140 °F					
Accessories:						
MP 2016	Mounting plate					

TEMPO 201x163x98

