

SOLID PC 2819 13 G-2FSH



Sample photo

Order symbol: PC 2819 13 G-2FSH
Product nbr: 2539509
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052711
EI. number:
Finland: 3435724
Electric No. Sweden: 2539509

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions: Length Width Height **Accessories:**

mm:	278	188	130
inch:	10.9	7.4	5.1

EKJXT	Mounting plate isolated
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKJZR	Extension frame

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:

Ingress Protection (EN 60529):	IP65
Impact Resistance (EN 62262):	IK08/IK09
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Certificates:

SGS Fimko
Gost R

Accessories:

EKJVT	Mounting plate
-------	----------------

