

**SOLID PC 2819 13 T-2FSH**



Sample photo

**Order symbol:** PC 2819 13 T-2FSH  
**Product nbr:** 2539539  
**Description:** Enclosure, PC  
**Remarks:** Transparent hinged cover

**EAN:** 6418074052834  
**EI. number:**  
**Finland:** 3435748  
**Electric No. Sweden:** 2539539

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

**Dimensions: Length Width Height Accessories:**

<b>mm:</b>	278	188	130	EKJXT	Mounting plate isolated
<b>inch:</b>	10.9	7.4	5.1	EKV 12	DIN-35 Mounting rail
				EKV 22	DIN-35 Mounting rail
				EKJZR	Extension frame

**Materials:**

**Material:** Polycarbonate  
**Base colour:** RAL 7035 -light grey  
**Cover screws material:** Polyamide  
**Cover colour:** Clear transparent  
**Cover screws colour:** Grey  
**Gasket material:** Polyurethane

**Rating:**

Ingress Protection (EN 60529): IP65  
 Impact Resistance (EN 62262): IK08/IK09  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 746C 5"  
 Glow Wire Test (IEC 695-2-1) °C: 960

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C  
**Temperature °C (continuous):** -40 ... 80 °C  
**Temperature °F (short term):** -40 ... 250 °F  
**Temperature °F (continuous):** -40 ... 175 °F

**Certificates:**

SGS Fimko  
 Gost R

**Accessories:**

EKJVT Mounting plate

