



Sample photo

**Order symbol:** PC 5628 13 G-3FSH  
**Product nbr:** 2539525  
**Description:** Enclosure, PC  
**Remarks:** Grey hinged cover

**EAN:** 6418074052759  
**EI. number:**  
**Finland:** 3435732  
**Electric No. Sweden:** 2539525

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
<b>mm:</b>	558	278	130	EKTX	Mounting plate isolated
<b>inch:</b>	22.0	10.9	5.1	EKV 22	DIN-35 Mounting rail
<b>Materials:</b>				EKV 50	DIN-35 Mounting rail
<b>Material:</b>	Polycarbonate			EKTZR	Extension frame

<b>Base colour:</b>	RAL 7035 -light grey	<b>Rating:</b>	
<b>Cover screws material:</b>	Polyamide	Ingress Protection (EN 60529): IP65	
<b>Cover colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08/IK09	
<b>Cover screws colour:</b>	Grey	Electrical insulation: Totally insulated	
<b>Gasket material:</b>	Polyurethane	Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperatures:</b>		UV resistance: UL 508	
<b>Temperature °C (short term):</b>	-40 ... 120 °C	Flammability Rating: UL 746C 5"	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Temperature °F (short term):</b>	-40 ... 250 °F	<b>Certificates:</b>	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F	SGS Fimko	
<b>Accessories:</b>		Gost R	

<b>Accessories:</b>	EKTVT	Mounting plate
---------------------	-------	----------------

