

**SOLID PC 5638 18 T**



Sample photo

**Order symbol:** PC 5638 18 T  
**Product nbr:** 5330065  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005618  
**EI. number:**  
 Finland: 3423823  
 Electric No. Italy: 7402065  
 Electric No. Sweden: 2539458

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	558	378	180	EKUXT	Mounting plate isolated
inch:	22.0	14.9	7.1	EKV 32	DIN-35 Mounting rail
				EKUZR	Extension frame

Materials:	
<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	Clear transparent
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08/IK09
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 250 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

Certificates:
SGS Fimko
Gost R

Accessories:	
EKUVT	Mounting plate

