

**ARCA 304015**



Sample photo

**Order symbol:** ARCA 304015  
**Product nbr:** 8120022  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074079336  
**EI. number:**  
 Finland: 3423119  
 Electric No. 8212091207  
 Denmark:  
 Electric No. Sweden: 2500111

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	300	400	150	MPP ARCA 3040	Mounting plate perforated (350x250x2 mm - 26x11 mm)
<b>inch:</b>	11.8	15.7	5.9	MPMP ARCA 4030	Mounting plate multiperforated (350x250x2 mm - □3.6 mm)
Materials:				MPX ARCA 4030	Mounting plate (350x250 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 304015	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			IDS ARCA 3040	Inner door set
<b>Cover colour:</b>	RAL 7035 -light grey			PMK ARCA 40	Pole mounting kit
<b>Gasket material:</b>	Polyurethane			RCS ARCA 3040	Rain canopy set
Temperatures:				SBK ARCA 30	Support bar kit
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 40	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
<b>Temperature °F (short term):</b>	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Accessories:					
MPS ARCA 4030	Mounting plate (350x250x2 mm)				

**Rating:**  
 Ingress Protection (EN 60529): IP66  
 Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 94 5VA  
 Glow Wire Test (IEC 695-2-1) °C: 960

**Certificates:**  
 SGS Fimko  
 Gost R

