

ARCA 608030



Sample photo

Order symbol: ARCA 608030
Product nbr: 8120029
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074085160
EI. number:
 Finland: 3424064
 Electric No. 8212095368
 Denmark:
 Electric No. Sweden: 2500121

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	600	800	300	MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
inch:	23.6	31.5	11.8	MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover colour:	RAL 7035 -light grey				
Gasket material:	Polyurethane				
Temperatures:					
Temperature °C (short term):	-40 ... 120 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MPS ARCA 8060	Mounting plate (730x530x2 mm)				
MPX ARCA 8060	Mounting plate (730x530 mm)				
IDS ARCA 6080	Inner door set				
PMK ARCA 80	Pole mounting kit				
RCS ARCA 6080	Rain canopy set				
SBK ARCA 60	Support bar kit				
SBK ARCA 80	Support bar kit				
DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060				
DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060				
Rating:					
Ingress Protection (EN 60529): IP66					
Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C					
Electrical insulation: Totally insulated					
Halogen free (DIN/VDE 0472, Part 815): 1					
UV resistance: UL 508					
Flammability Rating: UL 94 5VA					
Glow Wire Test (IEC 695-2-1) °C: 960					
Certificates:					
SGS Fimko					
Gost R					

